

Eaton Comet 18mm tubular photoelectric sensor

11102A6513

UPC:782113887067

Dimensions:

- **Height:** .71 IN
- **Length:** 2.75 IN
- **Width:** .47 IN

Warranties:

- 3 year

Specifications:

- **Cable Type:** PVC
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Polyurethane Foam (RIM)
- **Environmental Rating:** NEMA 1, 3, 4, 4X, 6, 12, 13, IP69k
- **Input Voltage:** 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
- **Led Indicators:** Power
- **Operating Temperature:** -4° to 158°F (-20° to 70°C)
- **Sensor Type:** Through Beam
- **Series:** Comet
- **Used With:** Used with 80 ft detectors

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Comet series - Photoelectric sensors](#)
- [Eaton Specification Sheet - 11102A6513](#)

Certifications:

- UL Recognized
- cUL Recognized

Product compliance: No Data



