

## Eaton XB IEC terminal block

**XBUT4BU**

**UPC:**782116894307

**Dimensions:**

- **Height:** 1.9 IN
- **Length:** .244 IN
- **Width:** .01 IN

**Weight:**.01 LB

**Warranties:**

- 1 year

**Specifications:**

- **Type:** IEC-XB Series
- **Amperage Rating:** 41A (IEC), 30A (EN), 38A (EN), 30A (UL)
- **Voltage Rating:** IEC 800V, EN 700V, UL 600V
- **Maximum Wire Size:** 10 AWG/4 mm<sup>2</sup>
- **Wire Size:** #26-10 AWG
- **Color:** Blue

**Supporting documents:**

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT4BU](#)

**Certifications:**

- CSA Certified
- UL Listed

**Product compliance:** No Data

