

Eaton definite purpose contactor

C25HNE3120A

UPC:782114182413

Dimensions:

- **Height:** 7.17 IN
- **Length:** 5.94 IN
- **Width:** 3.54 IN

Weight:8.7 LB

Notes:Resitive Load rating per pole

Warranties:

- 1 year

Specifications:

- **Connection:** Quick
- **Amperage Rating:** 120A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Size:** 120A, two- and three-pole
- **Resistive Load:** 140A
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [C25HNE3 2D PDF](#)
- [C25HNE3 3D Inventor](#)
- [C25HNE3 2D Drawing Xchange](#)
- [C25HNE3AutoCAD 2D Footprint \(mm\)](#)
- [C25HNE3 3D Model Xchange](#)
- [C25HNE3 AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - C25HNE3120A](#)

Certifications:



- UL Recognized
- CSA Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.