

## Eaton definite purpose contactor

**C25KNE3200A**

**UPC:**782114183939

### Dimensions:

- **Height:** 9.11 IN
- **Length:** 7.25 IN
- **Width:** 7.05 IN

**Weight:**21.9 LB

**Notes:**Resitive Load rating per pole

### Warranties:

- 1 year

### Specifications:

- **Connection:** Quick
- **Amperage Rating:** 200A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Contact Configuration:** 1NO, 1NC
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Size:** 200 and 300A, three-pole
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [C25KNE3 3D Model Xchange](#)
- [C25KNE3 2D PDF](#)
- [C25KNE3 3D Inventor](#)
- [C25KNE3 2D Drawing Xchange](#)
- [C25KNE3 AutoCAD 2D Footprint](#)
- [C25KNE3AutoCAD 2D Footprint \(mm\)](#)
- [Eaton Specification Sheet - C25KNE3200A](#)

### Certifications:



- CSA Certified
- UL Recognized

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.