



E47 Enclosed Precision Limit Switch

E47CLS05

UPC:782114993521

Dimensions:

- **Height:** 3.39 IN
- **Length:** 1 IN
- **Width:** 2.5 IN

Weight:.5125 LB

Notes:Bottom facing M4 x 0.7 (8-32) terminal screws with cup washers will accept 22 -12 AWG (2.5 sq. mm maximum)

Warranties:

- 1 year

Specifications:

- **Type:** E47 Enclosed Precision Limit Switch
- **Amperage Rating:** 20A
- **Connection:** Screw Terminals
- **Contact Rating:** 20A at 125Vac / 20A at 14Vdc
- **Contact Configuration:** SPDT
- **Enclosure Material:** Die Cast Aluminum
- **Environmental Rating:** NEMA 1
- **Operating Temperature:** 5° to 176°F (-15° to 80°C)
- **Switch Type:** Plunger Actuator

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [E47 precision - Limit switches](#)
- [Eaton Specification Sheet - E47CLS05](#)

Certifications: No Data

Product compliance:

- Contact factory

