

## Eaton definite purpose contactor

**C25DNJ350A**

**UPC:**782116300723

### Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.35 IN
- **Width:** 2.4 IN

**Weight:**1.3 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Accessories:** Mounting plate
- **Connection:** Quick
- **Auxiliary Contact:** Quick connect (vertical in-line)
- **Coil:** 110/120 Vac
- **Coil Voltage:** 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Inductive Full Load:** 50A
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Series:** E1
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25DNJ3 AutoCAD 2D Footprint \(mm\)](#)
- [C25DNJ3 3D Inventor](#)
- [C25DNJ3 2D Drawing Xchange](#)
- [C25DNJ3 3D Model Xchange](#)



- [C25DNJ3 2D PDF](#)
- [C25DNJ3 AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - C25DNJ350A](#)

**Certifications:**

- CSA Certified
- UL Listed file E1491 (Guide Number NLDX2)

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.