

Eaton definite purpose contactor

C25DNF330B

UPC:782116311347

Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.35 IN
- **Width:** 2.4 IN

Weight:1.3 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Quick
- **Amperage Rating:** 30A
- **Auxiliary Contact:** Quick connect (side-by-side)
- **Coil:** 208-240 Vac, 50/60 Hz
- **Coil Voltage:** 440-480 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Options:** Global listed
- **Resistive Load:** 40A
- **Series:** D1
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - C25DNF330B](#)

Certifications:

- UL Recognized
- CSA Certified
- UL Listed file E1491 (Guide Number NLDX2)



Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.