

Eaton definite purpose contactor

C25DNJ250A

UPC:782116300457

Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.35 IN
- **Width:** 2.4 IN

Weight:1.3 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Accessories:** Mounting plate
- **Connection:** Quick
- **Auxiliary Contact:** Quick connect (vertical in-line)
- **Coil Voltage:** 110-120 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Two-pole
- **Series:** E1
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25DNJ2 AutoCAD 2D Footprint](#)
- [C25DNJ2 2D Drawing Xchange](#)
- [C25DNJ2 AutoCAD 2D Footprint \(mm\)](#)
- [C25DNJ2 2D PDF](#)
- [C25DNJ2 3D Model Xchange](#)
- [C25DNJ2 3D Inventor](#)



- [Eaton Specification Sheet - C25DNJ250A](#)

Certifications:

- UL Listed file E1491 (Guide Number NLDX2)
- CSA Certified

Product compliance:

- RoHS Compliant
- CE Marked