

## Eaton SVX adjustable frequency drive

**SVX020A1-5A4B1**

**UPC:**782116929214

**Dimensions:**

- **Height:** 22 IN
- **Length:** 9.3 IN
- **Width:** 7.6 IN

**Weight:**40.8 LB

**Warranties:**

- 2 year

**Specifications:**

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC L
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR6
- **Horsepower:** 20 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 575 V

**Supporting documents:**

- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Product Datasheet - SVX020A1-5A4B1](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [9000X AFD User Manual](#)
- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX020A1-5A4B1](#)

**Certifications:**

- IEC 61800-2



- EN 61800-3 Level H
- UL 508C

**Product compliance:**

- Contact Manufacturer

---

© 2016 Eaton. All rights reserved.