

Eaton SVX adjustable frequency drive

SVX040A1-5A4B1

UPC:782116929245

Dimensions:

- **Height:** 24.8 IN
- **Length:** 10.1 IN
- **Width:** 9.3 IN

Weight:77.2 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC L
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR7
- **Horsepower:** 40 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 575 V

Supporting documents:

- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Product Datasheet - SVX040A1-5A4B1](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [9000X AFD User Manual](#)
- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX040A1-5A4B1](#)

Certifications:

- UL 508C



- IEC 61800-2
- EN 61800-3 Level H

Product compliance:

- Contact Manufacturer

© 2016 Eaton. All rights reserved.