

FEATURES & SPECIFICATIONS

INTENDED USE

The LED Wireless Speaker Worklight provides an easy and efficient way to light up a workspace, and enjoy music while you work. Wirelessly stream audio from Bluetooth®-enabled devices. Conduct phone calls hands free with speaker phone function. Ideal for use in workshops and office spaces, utility rooms, and garages.

CONSTRUCTION

Constructed of a metal housing with dual surround sound Bluetooth® speakers and a pull chain for easy on/off operation. The white acrylic lens provides even illumination on surfaces where tasks are performed. This Worklight is designed for suspended installation with aircraft cables. Available with 5' cord and plug.

ELECTRICAL

LEDs have a 50,000 hour L70 rated life. Provides a cool color temperature of 4000K with a CRI of 80. Starts reliably down to 0^{0} F.

Mode: SPSL produces 4000 lumens. Standard input = 42 watts. 95 lumens per watt.

Actual wattage may differ by +/- 5% when operating at 120V +/- 10%.

Standard with 120V driver (120V, 60Hz).

INSTALLATION

Includes 16" aircraft cables. Bluetooth range is 80 feet from source. Microphone range is 30 feet from source.

LISTINGS

CSA listed to US and Canadian safety standards. Damp Location rated.

WARRANTY

5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

NOTE: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.



Catalog

Number

Indoor General Purpose

SPSL LED Work Light

HIGH-PERFORMANCE LED WITH DUAL INTEGRATED WIRELESS SPEAKERS



😵 Bluetooth°

Dimensions

 Length:
 42.0 (106.6)

 Width:
 2.8 (7.0)

 Height:
 2.9 (7.4)

 Weight:
 4 lbs. (1.8 kg)

All dimensions are inches (centimeters) unless otherwise indicated.

ORDERING INFORMATION	For shortest lead times, configure product using	Example: SPSL 48IN 40K 80CRI BL		
Series	Length	ССТ	CRI	Finish

Series	Length	T)	CRI	Finish
SPSL	48IN 48 inches	40K	80CRI	BL Black

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Acuity Brands Lighting is under license. Lithonia Lighting is a trademark of Acuity Brands Lighting.

LED Shoplight

PHOTOMETRICS

Full photometric data report available within 2 weeks from request. Consult factory. Actual performance may differ as a result of end-user environment and application.

SPSL 48IN 40K 80CRI BL, test no. ISF 38653, tested in accordance to IESNA LM-79.

