

CONTINUOUS HINGE TWO-DOOR WITH 3-POINT LATCH, TYPE 4X

INDUSTRY STANDARDS

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997
 cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File Number E61997

NEMA Type 3, 3R, 4, 4X, 12, 13
 IEC 60529, IP66
 Meets NEMA Type 3RX requirements

APPLICATION

These two-door wall-mount enclosures provide industry-leading protection for components in corrosive or wet environments. Enclosures have a removable centerpost for easy panel installation, 3-point latching with Hoffman's exclusive POWERGLIDE Handles, and a seamless foam-in-place gasket for sealing protection from contaminants.

SPECIFICATIONS

- Manufactured from 14 gauge Type 304 stainless steel
- Seams continuously welded and ground smooth
- Removable centerpost for easy panel installation
- Flange trough collar around all sides of enclosure door openings
- External mounting brackets
- Heavy-duty 3-point latching mechanism operated by Type 316 stainless steel POWERGLIDE padlocking handles
- Easily removable doors by pulling heavy gauge continuous hinge pin
- Data pocket is high-impact thermoplastic
- Seamless foam-in-place gasket
- Collar studs provided for mounting optional panels
- Bonding provisions on doors; grounding studs on body

FINISH

Doors, sides, top and bottom have smooth #4 brushed finish.

ACCESSORIES

Floor Stand Kit, Stainless Steel
 PANELITE Enclosure Lights
 Panels for Type 3R, 4, 4X, 12 and 13 Enclosures
 Steel, Stainless Steel and Non-Metallic Window Kits
 H2OMIT Vent Drains, Type 4X
 H2OMIT Thermoelectric Dehumidifier

MODIFICATION AND CUSTOMIZATION

Hoffman excels at modifying and customizing products to your specifications. Contact your local Hoffman sales office or distributor for complete information.

BULLETIN: A4SW
Standard Product

| Catalog Number | AxBxC in./mm | Mild Steel Panel | Conductive Panel | Panel Gauge | Panel Size D x E in./mm | Y in./mm |
|--------------------|--|------------------|------------------|-------------|------------------------------|------------|
| A24H4208WFSSLP3PT | 24.00 x 42.00 x 8.00 610 x 1067 x 203 | A42P24 | A42P24G | 12 | 39.00 x 21.00 991 x 533 | 1.50 38 |
| A24H4808WFSSLP3PT | 24.00 x 48.00 x 8.00 610 x 1219 x 203 | A48P24 | A48P24G | 12 | 45.00 x 21.00 1143 x 533 | 1.50 38 |
| A30H4210WFSSLP3PT | 30.00 x 42.00 x 10.00 762 x 1067 x 254 | A42P30 | A42P30G | 12 | 39.00 x 27.00 991 x 686 | 1.50 38 |
| A30H4810WFSSLP3PT | 30.00 x 48.00 x 10.00 762 x 1219 x 254 | A48P30 | A48P30G | 12 | 45.00 x 27.00 1143 x 686 | 1.50 38 |
| A30H6010WFSSLP3PT | 30.00 x 60.00 x 10.00 762 x 1524 x 254 | A60P30 | A60P30G | 12 | 57.00 x 27.00 1448 x 686 | 1.50 38 |
| A36H4212WFSSLP3PT | 36.00 x 42.00 x 12.00 914 x 1067 x 305 | A42P36 | A42P36G | 12 | 39.00 x 33.00 991 x 838 | 1.50 38 |
| A36H4812WFSSLP3PT | 36.00 x 48.00 x 12.00 914 x 1219 x 305 | A48P36 | A48P36G | 12 | 45.00 x 33.00 1143 x 838 | 1.50 38 |
| A36H6012WFSSLP3PT | 36.00 x 60.00 x 12.00 914 x 1524 x 305 | A60P36 | A60P36G | 12 | 57.00 x 33.00 1448 x 838 | 1.50 38 |
| A42H4212WFSSLP3PT | 42.00 x 42.00 x 12.00 1067 x 1067 x 305 | A42P42 | A42P42G | 12 | 39.00 x 39.00 991 x 991 | 1.50 38 |
| A42H4812WFSSLP3PT | 42.00 x 48.00 x 12.00 1067 x 1219 x 305 | A48P42 | A48P42G | 12 | 45.00 x 39.00 1143 x 991 | 1.50 38 |
| A42H6012WFSSALP3PT | 42.00 x 60.00 x 12.00 1067 x 1524 x 305 | A60BFP42 | A60BFP42G | 10 | 56.00 x 38.00 1422 x 965 | 2.00 51 |
| A48H4812WFSSLP3PT | 48.00 x 48.00 x 12.00 1219 x 1219 x 305 | A48P48 | A48P48G | 10 | 44.00 x 44.00 1118 x 1118 | 2.00 51 |

Purchase panels separately. Optional stainless steel panels are available for most sizes.

Enclosure backs for A42H4212WFSSLP3PT, A42H4812WFSSLP3PT and A42H6012WFSSALP3PT have internal stiffeners.

A48H4812WFSSLP3PT is 14 gauge with a 12 gauge back.

