JUNO

SUPER SLOPE CEILING TC HOUSING

Project:

Fixture Type:

Location:

Contact/Phone:

PRODUCT DESCRIPTION

Slope ceiling TC Housing designed for use in non-insulated areas • If installed where insulation is present, the insulation must be pulled back 3" from all sides of the TC housing.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected – see reverse.

Socket Medium base porcelain with nickel-plated copper screw shell • Adjustable to position lamp perpendicular to floor.

Trims Trim selection shown on reverse.

Labels U.L. listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps or insulation • Union made • UL Listed/CSA certified • Trim No. 603 is wet location approved for covered ceiling applications.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Specifications subject to change without notice.

INSTALLATION

Real Nail 3 Bar Hangers Telescoping, Patented (US Patent D552,969) Real Nail 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edgemounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.


Junction Box Pre-wired junction box provided with (5) ½" and (1) ¾" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots.

Mounting Frame 22-gauge die-formed galvanized steel mounting frame • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation.

Housing TC housing, 22-gauge white painted steel with aluminum cap • Housing is vertically adjustable to accommodate up to a 1" ceiling thickness • Designed to fit 2x8 or 2x10 construction. SUPER SLOPE: 7/12 TO 12/12 PITCH (30°TO 45°) INCANDESCENT LAMPS TC928

G4.2.1

DIMENSIONS



PRODUCT CODES

Catalog Number		Input Voltage	Lamp Rating
TC928	6" Incandescent Super Slope Ceiling New Construction Non-IC Hsg	120V	PAR16/PAR38

Housing and trim can be ordered together or separate, but will always ship separately.

G4.2.1

SUPER SLOPE CEILING TC HOUSING

SUPER SLOPE: 7/12 TO 12/12 PITCH (30°TO 45°) INCANDESCENT LAMPS **TC928**

ROUND TRIMS

	Cat. No.	Description	Lamp Rating
\cap	602 BWH	6" Super Slope Downlight Cone Trim - Black Cone, White Trim Ring	75W PAR30, 150W PAR38, 85W BR30
	602 CWH	$6^{\prime\prime}$ Super Slope Downlight Cone Trim - Clear Alzak ® Cone, White Trim Ring	
	602 GWH	6" Super Slope Downlight Cone Trim - Gold Cone, White Trim Ring	
	602 HZSC	6" Super Slope Downlight Cone Trim - Haze Cone, Satin Chrome Trim	
	602 HZWH	6" Super Slope Downlight Cone Trim - Haze Cone, White Trim Ring	
	602 WHZBRZ	6" Super Slope Downlight Cone Trim - Wheat Haze Cone, Bronze Trim Ring	
	602 WHZWH	6" Super Slope Downlight Cone Trim - Wheat Haze Cone, White Trim Ring	
	602 WWH	6" Super Slope Downlight Cone Trim - White Cone, White Trim Ring	
D	603 BWH ◆	6" Lensed Flat Diffuser Trim - Black Baffle, White Trim Ring	75W A19, 75W PAR30
	603 WWH 🔶	6" Lensed Flat Diffuser Trim - White Baffle, White Trim Ring	
	604 BBRZ	6" Downlight Baffle Trim - Black Baffle, Bronze Trim Ring	150W PAR38
	604 BBL	6" Downlight Baffle Trim - Black Baffle, Black Trim Ring	
	604 BSC	6" Downlight Baffle Trim - Black Baffle, Satin Chrome Trim Ring	
	604 BWH	6" Downlight Baffle Trim - Black Baffle, White Trim Ring	
	604 WWH	6" Downlight Baffle Trim - White Baffle, White Trim Ring	
	606 BWH	6" Adjustable Cylinder Spotlight in Baffle Trim - Black Baffle, White Trim Ring	60W PAR16
	606 WWH	6" Adjustable Cylinder Spotlight in Baffle Trim - White Baffle, White Trim Ring	

Trim Size: Cat. No. 604 - 9 3/16" x 8 3/16" O.D, Cat. No. 606 - 9 1/8" O.D.

◆ UL Listed for use in wet location.