
MEDIUM BASE LAMPHOLDER

201 | [Pass & Seymour](#)



FEATURES & BENEFITS

Medium base, rubber, keyless, for temporary lighting, 2 wire leads 6" long. Black.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Medium Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CSA Listed: Yes
CSA Standard: C22.2 No. 42
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39111803
UR: No

DIMENSIONS

Diameter (US): 1.75"
Height (US): 1.75"

TECHNICAL INFORMATION

Volts: 600V

Volts (AC): 250

Watts: 660

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

