



TAMPER-RESISTANT FLOOR BOX ASSEMBLY - ONE GANG FOR WOOD SUB- FLOORS

FB1TRDRN | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Floor Box Assembly. #8 duplex opening. Two threaded screw plug, Includes 3232 15 amp, 125 volt tamper-resistant receptacle. Nickel.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

☐☐WARNING: This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information, go to www.P65Warnings.ca.gov.

- Tamper-Resistant shutters let plugs in, keep other things out.
- Rugged diecast cover plates.
- Meets UL514(c) and NEC 314.27(c).
- Scrub water compliant.
- With durable nickel or brass cover plates.
- Dual-voltage models available.
- Swing brackets mounting option eliminates drilling tile flooring for mounting screws.
- Wood sub-floors only.
- Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater

Component Type: Full Assemblies

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CSA Standard: Yes

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121308

UR: No

DIMENSIONS

Depth (US): 4

Length (US): 4.75

Width (US): 3.25

Volume: 20.5

TECHNICAL INFORMATION

Material: Nickel

Floor Type: Wood

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

