

Project Name

Location

Prepared By



SATCO S13121

70W/LED/HID/HP360/840/100-277V

Notes

[www] 11-02-2020 01:57:05

General

Status	Active
Watts	70
HID Equivalent	250
Volts	100V-277V
Shape	Comcob
Base	Mogul Extended
ANSI Base	EX39
Finish	Clear
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80+
Lumens	10500
Beam Spread	360
Dimmable	Dimmable with optional control modules
Hours Rated	50000
Lamp Type	LED HID
Technology	LED
Min Compartment Size	Width: 8 in. Height: 8 in. Depth: 10.75 in.

Electrical

Working Voltage	Direct wire range voltage 100-277V
Operating Frequency	50/60 Hz
Candlepower	3377
Dimming Type	Smart
Power Factor	>0.9
Burning Position	Universal
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-30C (-22F) to a maximum of +60C (140F)

Physical

MOL	11.59
MOD	7
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Housing Color	White
Photocell	Multiple Optional Sensors Available
Weight (lb.)	2.43

Additional Information

Additional Info	80-954 - Dimmable via WiFi accessory; 80-955 - Hi-Pro Motion Sensor / PIR; 80-956 - Hi-Pro Photocell; 80-957 - Hi-Pro Motion Sensor / MW
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Specification Note	This is not to be used with a ballast
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLVXJ87V5QLA
CEC Status	Lawful for sale in California
FCC Compliant	Yes
SDS Sheet	LED_Lamp

