



Main

Range of product	Stab-lok
Product or component type	Miniature circuit-breaker

Complementary

Line Rated Current	60 A
System Voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	2P
Breaking capacity	10 kA
Electrical connection	Screw connector
AWG gauge	AWG 4...AWG 2/0 aluminium/copper AWG 14...AWG 2 aluminium/copper

Environment

Product certifications	CSA
------------------------	-----

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--