



Main

Range of product	Stab-lok
Product or component type	Miniature circuit-breaker
Line Rated Current	30 A
System Voltage	120 V AC
Poles description	1P
Breaking capacity	10 kA

Complementary

Mounting mode	Plug-in
Electrical connection	Screw connector
AWG gauge	AWG 14...AWG 9 (copper)

Environment

Product certifications	CSA
------------------------	-----

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--