



### Main

Range of product	Stab-lok
Product or component type	Miniature circuit-breaker
Line Rated Current	40 A
System Voltage	120/240 V AC
Poles description	2P
Breaking capacity	10 kA

### Complementary

Mounting mode	Plug-in
Electrical connection	Screw connector
AWG gauge	AWG 14...AWG 6 (copper)

### Environment

Product certifications	CSA
------------------------	-----

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--