

Product data sheet

Characteristics

QO120

QO Mini CB 20 A 1P 120/240 V 10 kA Plug-in Mount

Product availability : Stock - Normally stocked in distribution facility



Price* : 29.10 USD



Main

Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	20 A
System Voltage	120 V AC 120/240 V AC 48 V DC
Mounting mode	Plug-in
Poles description	1P
Circuit breaker type	Standard
Circuit breaker application	HACR and Switching Duty rated
Electrical connection	Pressure plate

Complementary

Breaking capacity	10 kA at: 120/240 V AC 5 kA at: 48 V DC 10 kA at: 120 V AC
Number of spaces required	1
AWG gauge	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	0.75 in

Environment

Product certifications	UL listed CSA
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	00004 - QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
GTIN	00785901400103
Nbr. of units in pkg.	10
Package weight(Lbs)	0.28000000000000003
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------