

QO240

QO Mini CB 40 A 2P 120/240 V 10 kA Plug-in Mount

Product availability : Stock - Normally stocked in distribution facility



Price* : 67.00 USD



Main

Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	40 A
System Voltage	120 V AC 120/240 V AC 48 V DC
Mounting mode	Plug-in
Poles description	2P
Circuit breaker type	Standard
Circuit breaker application	HACR rated
Electrical connection	Box lugs

Complementary

Breaking capacity	10 kA at: 120/240 V AC 5 kA at: 48 V DC 10 kA at: 120 V AC
Number of spaces required	2
AWG gauge	AWG 8...AWG 2 (copper or aluminium)
Height	3.12 in
Depth	2.91 in
Width	1.5 in

Environment

Product certifications	CSA UL listed
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	00004 - QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
GTIN	00785901400486
Nbr. of units in pkg.	5
Package weight(Lbs)	0.57000000000000006
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------