

Product availability : Stock - Normally stocked in distribution facility



Price* : 233.00 USD



Main

Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	20 A
System Voltage	120 V AC
Mounting mode	Plug-in
Poles description	1P
Circuit breaker type	Ground fault protecting class A 6 mA
Circuit breaker application	Not rated
Electrical connection	Pressure plate

Complementary

Breaking capacity	10 kA at: 120 V AC
Number of spaces required	1
AWG gauge	AWG 14...AWG 8 (copper) AWG 12...AWG 8 (aluminium)
Height	4.12 in
Depth	2.91 in
Width	0.75 in

Environment


Product certifications	CSA UL listed
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	00003 - QO 1&2 POLE GFI CB 30A MAX
Discount Schedule	DE2A

GTIN	00785901255079
Nbr. of units in pkg.	1
Package weight(Lbs)	0.53000000000000003
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1340 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------