

NEW PRODUCT SHOWCASE



Strain Relief Connectors... New design for more flexibility

The **NEW** patent-pending Strain Relief Connectors come with everything needed to make a cable connection. The package includes a connector body, cap, and grommets that cover a wide range of cable types and sizes to provide added flexibility on the jobsite.

Designed to meet the new requirements of the product standard, these new specially designed grommets have collapsing teeth and an inverting membrane which secures cables and provides exceptional strain relief at termination points. The grommets are made from a specially formulated TPE material that provides exceptional grip and durability.

Four grommets cover a wide range of common round and oval cable sizes.

There are 3 round grommets in small, medium, and large sizes that cover round cable sizes from 0.335" to 0.575" and one oval grommet that covers oval cable sizes from 0.451" x 0.225" to 0.585" x 0.282".

Installation is simple and straightforward. Thread the cable through the cap, grommet, and body. Tighten the cap and affix the assembly to the enclosure using a junction box adapter and coupling (for solvent cement connections) or locknut (for threaded connections). The strain relief connectors are available in three configurations: 1/2" threaded, 3/4" threaded, and 3/4" solvent cement. The threaded options come with an O-ring and steel locknut.

Features & Benefits

- Creates a secure cord connection to junction boxes and enclosures
- Redesigned grommets for exceptional cord gripping strength
- Approved for indoor and outdoor use



Products are manufactured by IPEX Electrical Inc.

Size	Configuration	NEW Part Number	NEW Product Code	OLD Product Code
1/2"	Threaded	TSRC10A	277081	077754
3/4"	Threaded	TSRC15A	277079	077756
3/4"	Solvent Weld	SRC15A	277080	077985