

TYPE

SPAR

RocketSplice[®] Insulated Splicer-Reducer Connector




Features

- Transparent flexible insulating cover
- Range adjustable trim-to-fit tip
- Unique shape and compact design
- Connector, cover and cable tie packaged together
- UL Listed and CSA Certified for 600 volts
- Dual Rated

Benefits

- No taping and allows visual inspection of splice
- Ensures proper fit of cover to cable
- Provides ease of installation, versatility and
 approximately approximately and a provide in tight and
- serviceability of connections made in tight spacesProvides ease of ordering
- Ensures reliability
- Use with copper or aluminum conductor





Catalog	Wire	Dimensions			Screw
Number	Range	L	W	Н	Size & Shape
SPAR-4	4-14	3.30	1.55	.76	slotted
SPAR-2	2-14	3.83	1.75	.95	slotted
SPAR-1/0	1/0-14	4.80	1.94	1.14	3/16" socket head
SPAR-250	250kcmil-6	5.67	2.41	1.29	5/16" socket head
SPAR-350	350kcmil-10	6.17	3.29	1.79	5/16" socket head
SPAR-500	500kcmil-4	7.94	3.66	2.28	3/8" socket head

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG) Not suitable for direct burial.

DE-OX Oxide Inhibitor is recommended for all aluminum terminations. Tested to UL 486A/B, UL File E6207



TYPE

SPAR

RocketSplice® Insulated Splicer-Reducer Connector



Features

- Transparent flexible insulating cover
- Range adjustable trim-to-fit tip
- Unique shape and compact design
- Connector, cover and cable tie packaged together
- UL Listed and CSA Certified for 600 volts
- Dual Rated

Benefits

- No taping and allows visual inspection of splice
- Ensures proper fit of cover to cable
- Provides ease of installation, versatility and serviceability of connections made in tight spaces
- Provides ease of ordering
- Ensures reliability
- Use with copper or aluminum conductor



Catalog	Wire	Dimensions			Screw
Number	Range	L	W	Н	Size & Shape
SPAR-4	4-14	3.30	1.55	.76	slotted
SPAR-2	2-14	3.83	1.75	.95	slotted
SPAR-1/0	1/0-14	4.80	1.94	1.14	3/16" socket head
SPAR-250	250kcmil-6	5.67	2.41	1.29	5/16" socket head
SPAR-350	350kcmil-10	6.17	3.29	1.79	5/16" socket head
SPAR-500	500kcmil-4	7.94	3.66	2.28	3/8" socket head

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG) Not suitable for direct burial.

DE-OX Oxide Inhibitor is recommended for all aluminum terminations. Tested to UL 486A/B, UL File E6207