

YSP39T

by Burndy
Catalog ID: YSP39T

Prop 65 Notice

Uninsulated high voltage Cu -code compression splice, Tapered end, 750 kcmil, 600V-35KV, Tin plated, 24 Index.

Features: Seamless Types YSP-T High Conductivity Copper Electro-Tin Plated Compression HYLINK High-Voltage Splices With Long Barrel And Tapered Ends Are Ideally Suited For Higher Voltage Applications From 5KV Through 35 KV, Tapered Connector Ends Per EEI Standard TD160, Suitable For Use On Voltages 5KV Through 35KV To Aid In Preventing Corona Emission And Simplify Taping Thus Lowering Installed Cost, Type YSP-T Has A Center Plug Permanently Brazed In Place: Prevents Oil Within Oil-Filled Conductors From Passing Through The Splice Connector And Provides A Center Strip For Proper Conductor Insertion, Oil Stop: Yes, Tapered End: Yes, Die Index: 24 Element A, Conductor Type: Commercial Stranded Copper, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750, PAT750 Tool, U39RT Die, (4), Y46 Tool, U39RT Die With PUADP-1 Adapter, (4), Wire Strip Length: 2-1/8 IN



Product Details

General

Application	For Higher Voltage Applications From 5 KV Through 35 KV
Color Code	Black
Connector Type	Splice
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Electro Tin plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSP-T, High Voltage, Long Barrel
UPC	781810001349

Dimensions

Dimension - B Length inch	2.03 in
Dimension - L Length Overall mm	106 mm
Dimension - Length Overall inch	4.19 in
Dimension - Strip Length inch	2-1/8 in

Conductor Related

Conductor - Copper Str Size	750 kcmil
-----------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)