



## KS15

by Burndy  
Catalog ID: KS15

Prop 65 Notice

Copper Split Bolt, Cu: 10-8 AWG (Str) (Run & Tap).

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Installation Torque: 165 IN-LB, Length: 0.85 IN, Cross Flats: 0.5 IN, Width: 0.38 IN

## Product Details

### General

Application	For Direct Burial Applications In Earth Or Concrete, Copper
Connector Type	Split Bolt
Installation Torque Recommended in-lb	80 in-lbs
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810011256
UPC 12 Digit	7818100112566

### Dimensions

Dimension - B Length fraction	9/20 in
Dimension - B Length inch	.45 in
Dimension - Cross Flats inch	0.50 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.85
Dimension - Width fraction	19/50 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm
Width	0.38 in

### Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Run Range	10 AWG-8 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Solid Tap Range	14 AWG-8 AWG
Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG
Conductor - Copper Str Run Range	10 STR - 8 STR

Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	10 STR - 8 STR
Conductor - CopperWeld Solid Tap	#8
Conductor - CopperWeld Solid Tap Range	#8
Conductor - CopperWeld Str Run	#8
Conductor - CopperWeld Str Run Range	#8
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL486</li> <li>• UL467</li> <li>• CSA C22.2 No 41</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL486</li> <li>• UL467</li> <li>• CSA C22.2 No 41</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)