

YDS27

by Burndy
Catalog ID: YDS27

Prop 65 Notice

Hysplice, 3/0 (7, 19) Str., 7-1/4 in L, Full Tension Sleeve for All Copper Compressed and Compact Conductors.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U167/U568 Die, (7), Y45 Tool, U167/U568 Die With PT-6515 Adapter, (8), Y46 Tool, U167/U568 Die With PUADP-1 Adapter, (7), Die Index: 167 Element A, Conductor Type: Stranded Copper



Product Details

General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	167
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	7
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810014639

Dimensions

Dimension - B Length fraction	3-2/7 in
Dimension - B Length inch	3.29 in
Dimension - L Length Overall mm	173 mm
Dimension - Length Overall inch	6.83 in
Dimension - Outside Diameter inch	0.79 in

Conductor Related

Conductor - Copper Str Size	3/0 AWG
-----------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)