

YDS29

by Burndy
Catalog ID: YDS29

Prop 65 Notice

Hysplice, 250 (7, 19, 37) Str. , 7-1/2 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U169 Die, (9), Y45 Tool, U169 Die With PT-6515 Adapter, (9), Y46 Tool, U169 Die With PUADP-1 Adapter, (9), Y48B Tool, C169 Die, (3), Y60BHU Tool, L169 Die, (3), Die Index: 169 Element A, Conductor Type: Stranded Copper



Product Details

General

| | |
|--|--------------------------------|
| Application | For Stranded Copper Conductors |
| Connector Type | Splice |
| Die Index | 169 |
| Material | Copper |
| Oxide Inhibitor Type | Penetrox E |
| Physical Attribute - Number of Crimps Required | 3 |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Sub Brand | HYSPLICE |
| Trade Name | HYSPLICE™ |
| Type | YDS |
| UPC | 781810014646 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 3-1/2 in |
| Dimension - B Length inch | 3.54 in |
| Dimension - L Length Overall mm | 190 mm |
| Dimension - Length Overall inch | 7.47 in |
| Dimension - Outside Diameter inch | 0.95 in |

Conductor Related

| | |
|-----------------------------|-----------|
| Conductor - Copper Str Size | 250 kcmil |
|-----------------------------|-----------|

Certifications and Compliance

| | |
|-------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |

| | |
|------------------------------------|----|
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)