

# YC26L12

by Burndy  
Catalog ID: YC26L12

Prop 65 Notice

Copper Compression C Tap, Thin Wall, 1 AWG (Run), 2-1 AWG (Tap).

Features: Manufactured Form High Conductivity Wrought Copper: Provides Low Resistance And Excellent Electrical Conductivity, Range-Taking Connector: Lowers Inventory Requirements, Reinforced Ribs: Provides Maximum Pull-Out Values, Compact Size: Easy To Tape And Insulate Connection, Economical: Provides Low Installed Cost, Use PUADP-1 Adapter With U Dies In Y46 HYPRESS, Wire Strip Length: 1-13/16 IN, Color Code: Purple, Die Index: 15 Element A, Shape: C, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R, Y2MR Tool, W28VT Die, (3), Y35, Y39, Y750, Y45 Tool, UC26 Die, (1), Y46 Tool, UC26 Die With PUADP-1 Adapter, (1), Number Of Ribs: 2



## Product Details

### General

Application	For Making Copper Tap And Parallel Connections
Color Code	Purple
Connector Type	C-Tap
Die Index	15
Material	Copper
Plated	Y
Plating Type	Tin - Bright
Sub Brand	CRIMPIT
Temperature Rating	194
Type	YC-L Series
UPC	781810040188
UPC 12 Digit	7818100401888

### Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.69 in
Dimension - D inch	1.75 in
Dimension - Pad Width inch	0.43 in
Dimension - Strip Length inch	1-13/16

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Run	1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	1 AWG-2/0 AWG

Conductor - Copper Str Tap	12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	12 AWG-2 AWG

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)