

# YSS6R

by Burndy  
Catalog ID: YSS6R

Prop 65 Notice

Single aluminum sleeve designed for service drop or short span overhead distribution lines, Die index: 162.

Features: Single Aluminum Sleeve Designed For Service Drop Or Short Span Overhead Distribution Lines, Installed With OH25 One-Hand Tool, And Other Standard Tooling, Pre-Filled With PENETROX Joint Compound And Color Coded Capped, Holding Strength: ACSR: 900 LB, Aluminum: 700 LB, Die Index: 162 Element A, Conductor Type: ACSR, Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W162 Die, (4), Y35, Y750 Tool, U162 Die, (2), Y45 Tool, U162 Die With PT-6515 Adapter, (2), Y46 Tool, U162 Die With PUADP-1 Adapter, (2), Color Code: Blue



## Product Details

### General

Application	For Aluminum, ACSR, 6201, 5005 And Compressed Conductors And Service Drop Or Short Span Overhead Distribution Lines
Color Code	Blue
Connector Type	Splice
Die Index	162
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YSS
UPC	781810169704
UPC 12 Digit	7818101697044

### Dimensions

Dimension - B Length fraction	2-3/10 in
Dimension - B Length inch	2.3 in
Dimension - L Length Overall mm	120 mm
Dimension - Length Overall inch	4.72 in
Dimension - Outside Diameter inch	0.39 in

### Conductor Related

Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - AL Str Size	4 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)