



# YGHC34C26

Catalog ID: YGHC34C26

Prop 65 Notice

Copper Compression C Connector, 300-500 kcmil, 3/4" Rod (Run) & 6 AWG(Sol) - 2/0 AWG(Str) (Tap).

Features: Irreversible Compression Ground Tap Figure C Connectors, Accommodates All Cable Combinations From #6 AWG Solid Through 500 KCMIL, C- Shaped Opening Permits Placing Two Continuous Parallel Cables Into Conductor Groove, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Prefilled With PENETROX Compound And Strip Sealed, Certain Sizes Are Also UL467 Listed And CSA Certified For Wire To Ground Rod, Conductor Size (tap - Mm): 10 - 70 SQ-MM, Die Index: 1011 Element A, Conductor Size (run - Mm): 150 - 240 SQ-MM, Tools, Die Set Catalog Number, And (number Of Crimps): HYPRESS: Y35, Y39, Y750, PAT750 Tool, U1011 Die, (2), Y45 Tool, S1011 Die, (2), Y46 Tool, P1011 Die, (2), Ground Rod Size: 3/4 IN, Conductor Type: Run: Commercial Stranded Copper, Metric Copper, Tap: Commercial Stranded Copper, Metric Copper, Conductor Size (tap Range): 6 - 2/0 AWG, Shape: C, Conductor Size (run - Range): 300 - 500 KCMIL

#### **Product Details**

#### General

Application	For Direct Burial Cables
Connector Type	Тар
Die Index	1011
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, HYTAP
Trade Name	HYTAP™
Туре	Taps
UPC	781810221068
UPC 12 Digit	7818102210688

#### Dimensions

Dimension - B Length inch	0.88 in
Dimension - Height fraction	2-21/50 in
Dimension - Height inch	2.42 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

## Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-3/0 AWG
Conductor - Copper Str Run	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	300 kcmil-500 kcmil

Conductor - Copper Str Tap	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	7 AWG-2/0 AWG
Conductor - Rod Run	3/4 in
Conductor - Rod Run Range	3/4 in

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul><li>UL467</li><li>IEEE 837</li><li>UL468A-468B</li></ul>
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1	

#### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)