



## KLU35

by Burndy  
Catalog ID: KLU35

Prop 65 Notice

Copper Terminal, Offset Tongue, 1 Hole, 14 AWG (Sol)-6 AWG (Str), #10 Stud, 1 Screw.

Features: Convenient Range-Taking Design: One Conductor Accommodates Several Conductor Sizes, High Conductivity Copper Alloy: Long Lasting Reliable Contact, Compact Design: Easy To Use, Reduces Labor Time, Slot Robertson Screw, Hex Head/Hex Socket Bolt: No Special Installation Tools Required, Eliminates Over-Torquing/Potential Conductor Damage, High Copper Alloy Terminal With Offset Tongue For Joining A Wide Range Of Cable To Equipment Pads Or Bar, Easy To Install With Screwdriver Or Wrench, Connector Is Reusable, Plain Copper Finish, For Copper Cable, Wire Strip Length: 5/8 IN, Stud/bolt Size: 1/4 IN, Stud/bolt Hole Size: #10, Dimension N: 0.22 IN, Set Screw Type: Slot Robertson, Installation Torque: 45 IN-LB, Length: 1.24 IN, Width: 0.39 IN, Tongue Width : 0.38 IN, Dimension B: 0.33 IN, Dimension K: 0.2 IN, Dimension T: 07 IN

## Product Details

### General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar
Connector Type	Terminal
Hardware Type	1/4 UNF Slotted SetScrew
Installation Torque Recommended in-lb	35
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810351376

### Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.43 in
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.24 in
Dimension - N inch	0.22 in
Dimension - Pad Width inch	0.39 in

Dimension - Screw Size inch	1/4
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	#10

### Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	14 AWG-6 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	14 AWG-6 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)