

YS36

by Burndy
Catalog ID: YS36

Prop 65 Notice

Copper Compression Splice, 600 kcmil, 5.85" Splice Length, Long Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 Volts to 35 kV, Long Barrel Length: Ideal For 600 Volt Heavy Duty Applications, Also May Be Used At Higher Voltages Up To 35KV, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Much Greater Mechanical And Electrical Properties, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (4), Tapered End: No, Oil Stop: No, Color Code: Green, Die Index: 22 Or 472, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750 Tool, U36RT Die, (4), Y46 Tool, U36RT Die With PUADP-1 Adapter, (4), Conductor Type: Commercial Stranded Copper, Wire Strip Length: 2-3/4 IN



Product Details

General

Application	For Heavy Duty Applications And Used At Higher Voltages Up To 35 KV
Color Code	Green
Connector Type	Splice
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS, Long Barrel
UPC	781810526255
UPC 12 Digit	7818105262555

Dimensions

Dimension - B Length inch	2.63 in
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.85 in
Dimension - Strip Length inch	2-11/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	600 kcmil
-----------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)