



# TP168F

by Burndy Catalog ID: TP168F

Prop 65 Notice

Copper Terminal, Fork Tongue, 22-16 AWG, #6-#8 Stud, Vinyl Insulated, Tin Plated.

Features: The Type TP-F Is A Fork Tongue Variation Of The TP Design And Makes Installation Easier, 600 V Maximum, 105 DEG C Max, Fork Tongue Design: Faster Installation-Screw Needs Only To Be Loosened For Termination, Tape Mounted Catalog Number: BA16EF8M, Insulation Diameter (maximum): 0.145 IN, Bulk Catalog Number: BA16EF8, Temperature Rating: 105 DEG C Maximum, Installation Tool: Plier Type: Y10-22 Tool, Ratchet: MR8-89-1 Tool, Wire Strip Length: 13/64 IN, Color Code: Red, Wire Insulation Grip: No, Finish: Electro-Tin Plated

# **Product Details**

General
---------

Application	For Commercial And Light Duty Industrial Control And Power Circuit Applications
Color Code	Red
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Υ
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Υ
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Туре	TP-F
UPC	781810714683
UPC 12 Digit	7818107146833

#### Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Hole Size fraction	9/53
Dimension - Hole Size inch	0.17 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.86 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#8

Dimension - Z inch	0.26 in

# **Electrical Ratings**

Voltage - Maximum	600 V
-------------------	-------

### **Conductor Related**

Conductor Range	#20 AWG to #22 AWG; 16 AWG to 18 AWG
Conductor Type	<ul><li>CU C Solid-Size</li><li>CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

#### Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

#### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)