



* Representative image

UDIEKITAL

by Burndy
Catalog ID: UDIEKITAL

Prop 65 Notice

Stainless Steel U Die Kit and Case for Aluminum Connectors (15 Set).

Features: The UDIEKITAL Die Kit Includes 15 Sets Of U Dies And The PT29291 Die Case, These Stainless Steel Color Coded Dies Are For Crimping BURNDY YA, YS, YA-A And YS-A Type HYLUG And HYLINK Color Coded Terminals And Splices Ranging From 6 AWG Through 750 KCMIL, BURNDY U Dies Are Used In The Y35, Y39, Y750 Series, PAT750-18V Series, Y46, And PAT46-18V (With PUADP-1 Adapter) Tools, Includes: U6CABT: 6 AWG Aluminum Wire, U4CABT: 4 AWG Aluminum Wire, U2CABT: 2 AWG Aluminum Wire, U1CART: 1 AWG Aluminum Wire, U25ART: 1/0 AWG Aluminum Wire, U26ART: 2/0 AWG Aluminum Wire, U27ART: 3/0 AWG Aluminum Wire, U28ART: 4/0 AWG Aluminum Wire, U29ART: 250 KCMIL Aluminum Wire, U30ART: 300 KCMIL Aluminum Wire, U31ART: 350 KCMIL Aluminum Wire, U32ART: 400 KCMIL Aluminum Wire, U34ART: 500 KCMIL Aluminum Wire, U36ART: 600 KCMIL Aluminum Wire, U39ART2: 750 KCMIL Aluminum Wire, PT29291 Die Case

Product Details

General

Application	Crimping
Construction Material - Main	Stainless Steel
Die Type	U DIE
Sub Brand	U-DIE SET
Type	U-Die Kit
UPC	781810480816
UPC 12 Digit	7818104808166

Conductor Related

Crimping Ranges	Aluminum: #6 AWG - 750 kcmil
-----------------	------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	U6CABT, U4CABT, U2CABT, U1CART, U25ART, U26ART, U27ART, U28ART, U29ART, U30ART, U31ART, U32ART, U34ART, U36ART, U39ART-2, PT29291

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)