



GXP1828RF

by Burndy
Catalog ID: GXP1828RF

Prop 65 Notice

Cast Copper Alloy Raised Floor Ground Connector, #6 Sol.-4/0 Str. , 4.53 in L, 3.94 in W.

Features: RAISED FLOOR, Installation Torque: 120 IN-LB

Product Details

General

Application	Used on applications which requiring multiple conductor sizes and/or configurations.
Installation Torque Recommended in-lb	120 LBS/in
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	SUPER-CLAMP
Trade Name	SUPER-CLAMP™
Type	GXP1828RF
UPC	781810503133
UPC 12 Digit	7818105031333

Dimensions

Dimension - Height inch	1.96 in
Dimension - Length Overall inch	4.53 in
Dimension - Pad Width inch	3.94 in

Conductor Related

Conductor - Copper Solid Size A	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size A Range	6 AWG-4/0 AWG
Conductor - Copper Solid Size B	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size B Range	6 AWG-4/0 AWG
Conductor - Copper Str Size A	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size A Range	6 AWG-4/0 AWG
Conductor - Copper Str Size B	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size B Range	6 AWG-4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)