

YCS28

by Burndy
Catalog ID: YCS28



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, 3-1/8 IN L.

Features: Loop HYSPLICE Connector Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Pure Copper Tubing, Installed With Standard HYSPLICE Tools And Dies, Tools, Die Set Catalog Number, And (number Of Crimps): Y750, Y35 Tool, U168 Die, (3), Y45 Tool, U168 Die With PT-6515 Adapter, (3), Y46 Tool, U168 Die With PUADP-1 Adapter, (3), Y48B Tool, C168 Die, (1), Y60BHU Tool, L168 Die, (1), Die Index: 168 Element A, Conductor Type: Copper

Product Details

General

Application	For Copper Conductors
Connector Type	Splice
Die Index	168
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS
UPC	781810014219
UPC 12 Digit	7818100142199

Dimensions

Dimension - A Outside Diameter inch	0.89 in
Dimension - B Length fraction	1-8/17 in
Dimension - B Length inch	1.47 in
Dimension - B Outside Diameter inch	0.89 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.09 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)