



YPC33R26U

by Burndy Catalog ID: YPC33R26U

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors,Run,Al and Cu:250 (37) - 400 (37).

Features: Extra Wide Range Universal Connector, Two Dies And 5 Connectors Take Run Sizes 1/0- 600 KCMIL, And Tap Sizes 6-400 KCMIL, Wide Range Made Possible By Long Ram Travel Of BURNDY HYPRESS Tools, Figure 6- Shape Separates Run And Tap Wires, And Minimizes Galvanic Corrosion Of Conductors, Connector Can Be Gripped In Tool And Slipped Over Line For Easy Installation, Pre-Filled With PENETROX Joint Compound And Stripsealed, Conductor Type: ACSR, 5005, Aluminum And Copper, Die Index: N Element A, Shape: 6, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-N Die, (2), Y45 Tool, S-N Die, (2), Y46 Tool, P-N Die, (2)

Product Details

General

Application	For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors	
Die Index	N	
Material	Aluminum	
Plated	N	
Plating Type	Unplated	
Sub Brand	CRIMPIT	
Trade Name	CRIMPIT™	
Туре	YPC-U	
UPC	781810137505	
UPC 12 Digit	7818101375055	

Dimensions

Dimension - Height inch	2.28 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.125 in
Dimension - Width inch	1.16 in

Conductor Related

Conductor - ACSR Str Run Range	266.8 kcmil-397.5 kcmil
Conductor - ACSR Str Tap Range	6 AWG- 1/0 AWG
Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Run Range	250 kcmil-400 kcmil
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Tap Range	6 AWG-2/0 AWG
Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil
Conductor - Copper Str Run Range	250 kcmil-400 kcmil
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG

Conductor - Copper Str Tap Range	6 AWG-2/0 AWG
Conductor Type	 AL C Str-Run CU C Str-Run CU C Solid-Run ACSR C Str-Run AL C Str-Tap CU C Str-Tap CU C Solid-Tap ACSR C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	1	

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)