

CT30125M

by Burndy
Catalog ID: CT30125M

Natural Nylon 6/6 Cable Tie, 1.25" Max. Bundle Dia, 30 Lbs, 6" Long, 0.14" Wide.

- Standard Cable Tie
- Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT1, MK7 Tool



Product Details

General

Application	For General Purpose
Color	Natural
Material	Nylon 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	30
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Intermediate
UPC	781810331910

Dimensions

Dimension - Bundle Diameter Max inch	1.25
Dimension - L Length Overall mm	146 mm
Dimension - Length Overall inch	5.75 in
Dimension - Width inch	0.14 in
Dimension - Width mm	3.6 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	Yes
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-5-9
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5000 EA
Minimum Pack Quantity	1000

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)