

PRODUCT-DETAILS

# CI4004-BAR

## PLASTIC CONNECTOR 1/2 10000/BARRE



### General Information

Extended Product Type	CI4004-BAR
Product ID	7TBA011030R0018
EAN	0622538077202
Catalog Description	PLASTIC CONNECTOR 1/2 10000/BARRE
Long Description	Connector, Non-Metallic Sheathed Cable, Size 1/2 Inch, Total Length 15/16 Inch, Width 7/8 Inch, Clamping Range Minimum 0.21 Inch to Maximum 0.42 Inch, Non-Metallic, Suggested Application 14/2-10/2, 14/3-10/3 2 Cables: 14/2-12/2, Pack of 10,000

### Ordering

EAN	0622538077202
Customs Tariff Number	3917400090

### Dimensions

Product Net Weight	.009 lb 4.082 g
--------------------	--------------------

### Container Information

Package Level 2 Units	10000 piece
Package Level 2 Width	18.75 in 476 mm

Package Level 2 Height	33 in 838 mm
Package Level 2 Depth / Length	18.75 in 476 mm

## Additional Information

Application	For 14/2-10/2; 14/3-10/3 2 cables: 14/2-12/2
Brand / Label	Iberville
Material	Plastic
Number of Batteries	0
Product Name	PLASTIC CABLE CONNECTOR, FITTING
Product Type	Nonmetallic Sheathed Cable
Size	1/2 Inch
Standards	UL E17583
UPC	622538077202

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	CI4004-BAR
Instructions and Manuals	CI4004-BAR

## Classifications

ETIM 6	EC001178 - Screw connection for protective plastic hose
ETIM 7	EC001178 - Screw connection for protective plastic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Commercial Fittings

