

PRODUCT-DETAILS

BR-075-150

NON-JKTD FLEX COND STL.75 INX150ME



General Information

Extended Product Type	BR-075-150
Product ID	7TBD012980R0154
EAN	0786210380223
Catalog Description	NON-JKTD FLEX COND STL.75 INX150ME
Long Description	Non-jacketed Flexible Conduit Steel 3/4 Inch X 150m

Ordering

EAN	0786210380223
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	.36 lb 163.265 g
--------------------	---------------------

Container Information

Package Level 2 Units	150 m
Package Level 2 Width	1 in 25 mm
Package Level 2 Height	1 in 25 mm

Package Level 2 Depth /
Length

1 in
25 mm

Additional Information

Application	Combustible or Non-Combustible Constructions
Brand / Label	T&B Industrial Fitting
Inside Diameter	0.812 in 20.6 mm
Material	Steel
Nominal Size	3/4 in
Number of Batteries	0
Outside Diameter	1.105 in 28.1 mm
Product Name	T&B LIQUIDTIGHT FITTINGS
Product Type	Flexible Conduit - Steel Core
Radius	4.0 in 101.6 mm
Special Functions	Formed From High Corrosion Resistant Hot-dipped Galvanized Steel. Its Profile and Helical Shape Allow it to Withstand Impact and Crushing Forces
Standards	UL Listed
Surface Finishing	Hot-Dipped Galvanized
UPC	786210380223

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	BR-075-150
Instructions and Manuals	BR-075-150

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Liquidtight Fittings

