



Powering Business Worldwide

7501V-C

Switch Decorator SP 15A 120/277V IV Can

UPC: 032664643453

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Single & Duplex Receptacles

Special Features: Wiring Type Back Wire and Side Wire

Application: Commercial grade dec

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, PVC Base

Color: White

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 0.82X 1.32X 1.98X4.19IN

Environmental Conditions: See Spec Sheet

Dielectric Strength: 2000 V

Insulation: Nylon Face, PVC Base

Temperature Rating: -20C to 70C (-4F to 158F)

7501V-JP;51

7501V Sold in Boxes of 10 Can

UPC: 032664643569