



Powering Business Worldwide

7501W-C

Switch Decorator SP 15A 120/277V WH Can

UPC: 032664643460

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single, Decorator, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Commercial grade dec
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: Nylon Face, PVC Base
Color: White
NEMA Rating: 5-20R
Mounting: Flush
Connection: Screw
Size: 1.32 In Width X 0.82 In Depth
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Nylon Face, PVC Base
Temperature Rating: -20C to 70C (-4F to 158F)

7501W-JP;51

7501W Sold in Boxes of 10 Can

UPC: 032664643583

Brand Name: Cooper Wiring Devices
Sub Brand: ARROW HART
Type: Duplex, Decorator, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Commercial
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: Nylon Face, PVC Base
Color: Black
NEMA Rating: 5-20R
Connection: Screw
Size: 1.32 In Width X 0.82 In Depth X 4.19 In Height