



Powering Business Worldwide

### 7503V-C

Switch Deco 3Way 15A 120/277V IV Can<sub>n</sub>

UPC: 032664643484

Brand Name: Cooper Wiring Devices  
Sub Brand: ARROW HART  
Type: Single, Straight Blade, Square<sub>n</sub>  
Special Features: Fiber Back and Steel Clips  
Application: Commercial  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 12 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 125 Vac  
Material: Urea Face, Polypropylene Base  
Color: Black  
NEMA Rating: 5-15R  
Mounting: Snap-In  
Connection: Quick Connect, Wire Lead

### 7503V-JP;51

7503V Sold in Boxes of 10 Can

UPC: 032664643606

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Single, Straight Blade, Square  
Special Features: Fiber Back and Steel Clips  
Application: Snap-in rcpts  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 12 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 125 Vac  
Material: Urea Face, Polypropylene Base  
Color: White  
NEMA Rating: 5-15R  
Mounting: Snap-In  
Connection: Quick Connect, Wire Lead  
Size: 1.81 X 2.50 X 3.28 IN  
Environmental Conditions: See Spec Sheet  
Dielectric Strength: 2000 V  
Insulation: Urea Face, Polypropylene Base  
Temperature Rating: -20C to 70C (-4F to 158F)