

Tmax T ranges

Ordering details T7

Tmax T7 Electronic protection (Molded case circuit breaker)

Standard PR231 LS/I version

Electronic trip unit				IC Rating (600V)	S 25 kA Part number	H 50 kA Part number	L 65 kA Part number
Frame size [A]	L adj. [A]	I adj. [A]	Poles				
1000	400...1000A	1000...10000A	3	T7S1000BW	T7H1000BW	T7L1000BW	
			4	T7S1000BW-4	T7H1000BW-4	T7L1000BW-4	
1200	480...1200A	1200...12000A	3	T7S1200BW	T7H1200BW	T7L1200BW	
			4	T7S1200BW-4	T7H1200BW-4	T7L1200BW-4	

Standard PR232 LSI version

Electronic trip unit				IC Rating (600V)	S 25 kA Part number	H 50 kA Part number	L 65 kA Part number
Frame size [A]	L adj. [A]	I adj. [A]	Poles				
1000	400...1000A	1000...12000A	3	T7S1000CW	T7H1000CW	T7L1000CW	
			4	T7S1000CW-4	T7H1000CW-4	T7L1000CW-4	
1200	480...1200A	1200...14400A	3	T7S1200CW	T7H1200CW	T7L1200CW	
			4	T7S1200CW-4	T7H1200CW-4	T7L1200CW-4	

Standard PR331 LSIG version

Electronic trip unit				IC Rating (600V)	S 25 kA Part number	H 50 kA Part number	L 65 kA Part number
Frame size [A]	L adj. [A]	I adj. [A]	Poles				
1000	400...1000A	1000...12000A	3	T7S1000EW	T7H1000EW	T7L1000EW	
			4	T7S1000EW-4	T7H1000EW-4	T7L1000EW-4	
1200	480...1200A	1200...14400A	3	T7S1200EW	T7H1200EW	T7L1200EW	
			4	T7S1200EW-4	T7H1200EW-4	T7L1200EW-4	

Standard PR332 LI version

Electronic trip unit				IC Rating (600V)	S 25 kA Part number	H 50 kA Part number	L 65 kA Part number
Frame size [A]	L adj. [A]	I adj. [A]	Poles				
1000	400...1000A	1000...15000A	3	T7S1000PW	T7H1000PW	T7L1000PW	
			4	T7S1000PW-4	T7H1000PW-4	T7L1000PW-4	
1200	480...1200A	1200...18000A	3	T7S1200PW	T7H1200PW	T7L1200PW	
			4	T7S1200PW-4	T7H1200PW-4	T7L1200PW-4	

Standard PR332 LSI version

Electronic trip unit				IC Rating (600V)	S 25 kA Part number	H 50 kA Part number	L 65 kA Part number
Frame size [A]	L adj. [A]	I adj. [A]	Poles				
1000	400...1000A	1000...15000A	3	T7S1000RW	T7H1000RW	T7L1000RW	
			4	T7S1000RW-4	T7H1000RW-4	T7L1000RW-4	
1200	480...1200A	1200...18000A	3	T7S1200RW	T7H1200RW	T7L1200RW	
			4	T7S1200RW-4	T7H1200RW-4	T7L1200RW-4	

Standard PR332 LSIG version

Electronic trip unit				IC Rating (600V)	S 25 kA Part number	H 50 kA Part number	L 65 kA Part number
Frame size [A]	L adj. [A]	I adj. [A]	Poles				
1000	400...1000A	1000...15000A	3	T7S1000SW	T7H1000SW	T7L1000SW	
			4	T7S1000SW-4	T7H1000SW-4	T7L1000SW-4	
1200	480...1200A	1200...18000A	3	T7S1200SW	T7H1200SW	T7L1200SW	
			4	T7S1200SW-4	T7H1200SW-4	T7L1200SW-4	