

Tmax T ranges

T8 Accessories

Terminals for base and circuit breaker

Rear terminals and front terminals for cables

Terminal type	T8	
	3p Part number	4p Part number
Vertical rear terminals	KT8VR2500	KT8VR2500-4
4x 1/0 to 4x 750 Kcmil (1600A rated)	KT8TL	—
6x 1/0 to 6x 750 Kcmil (1200A rated)	KT8TM	—

Phase separators

Type	T8	
	3p Part number	4p Part number
High profile	KT8PBH-3	KT8PBH-4
Low profile	KT8PBL-3	KT8PBL-4

Electrical operators

Shunt opening release (Y0)

Control voltage type	T8	
	Part number	
24V ac/dc	KT8ES0	
30V ac/dc	KT8ES9	
48V ac/dc	KT8ES8	
60V ac/dc	KT8ES7	
110...120V ac/dc	KT8ES6	
120...127V ac/dc	KT8ES5	
220...240V ac/dc	KT8ES4	
250V ac/dc	KT8ES3	
380...440Vac	KT8ES2	
440...480Vac	KT8ES1	

Second shunt opening release (Y02)

Control voltage type	T8	
	Part number	
24V ac/dc	KT8ES0-2	
30V ac/dc	KT8ES9-2	
48V ac/dc	KT8ES8-2	
60V ac/dc	KT8ES7-2	
110...120V ac/dc	KT8ES6-2	
120...127V ac/dc	KT8ES5-2	
220...240V ac/dc	KT8ES4-2	
250V ac/dc	KT8ES3-2	
380...440Vac	KT8ES2-2	
440...480Vac	KT8ES1-2	



Tmax T ranges

T8 Accessories

4



Undervoltage opening release (YU)

Control voltage type	T8
	Part number
24V ac/dc	KT8EU0
30V ac/dc	KT8EU9
48V ac/dc	KT8EU8
60V ac/dc	KT8EU7
110...120V ac/dc	KT8EU6
120...127V ac/dc	KT8EU5
220...240V ac/dc	KT8EU4
250V ac/dc	KT8EU3
380...440Vac	KT8EU2
440...480Vac	KT8EU1



Shunt closing release (YC)

Control voltage type	T8
	Part number
24V ac/dc	KT8EC0
30V ac/dc	KT8EC9
48V ac/dc	KT8EC8
60V ac/dc	KT8EC7
110...120V ac/dc	KT8EC6
120...127V ac/dc	KT8EC5
220...240V ac/dc	KT8EC4
250V ac/dc	KT8EC3
380...440Vac	KT8EC2
440...480Vac	KT8EC1

Motor operators

Spring charging motor operators

Control voltage type	T8
	Part number
24...30V ac/dc	KT8EM9
48...60V ac/dc	KT8EM7
110...130V ac/dc	KT8EM5
220...250V ac/dc	KT8EM3

