

Tmax T ranges

Ordering details T8

Tmax T8 Electronic protection (Molded case circuit breaker)

Standard PR331 LSI version

Electronic trip unit				IC	V
Frame size [A]	L adj. [A]	I adj. [A]	Poles	Rating (600V)	100 kA Part number
1600	640...1600A	1600...24000A	3		T8V16CW
			4		T8V16CW-4
2000	800...2000A	2000...30000A	3		T8V20CW
			4		T8V20CW-4
2500	1000...2500A	2500...37500A	3		T8V25CW
			4		T8V25CW
3000 ⁽¹⁾	1200...3000A	3000...45000A	3		T8V30CW
			4		T8V30CW-4

⁽¹⁾ Only available with rear vertical terminals for busbars

Standard PR331 LSIG version

Electronic trip unit				IC	V
Frame size [A]	L adj. [A]	I adj. [A]	Poles	Rating (600V)	100 kA Part number
1600	640...1600A	1600...24000A	3		T8V16EW
			4		T8V16EW-4
2000	800...2000A	2000...30000A	3		T8V20EW
			4		T8V20EW-4
2500	1000...2500A	2500...37500A	3		T8V25EW
			4		T8V25EW
3000 ⁽¹⁾	1200...3000A	3000...45000A	3		T8V30EW
			4		T8V30EW-4

⁽¹⁾ Only available with rear vertical terminals for busbars

Standard PR332 LI version

Electronic trip unit				IC	V
Frame size [A]	L adj. [A]	I adj. [A]	Poles	Rating (600V)	100 kA Part number
1600	640...1600A	1600...24000A	3		T8V16PW
			4		T8V16PW-4
2000	800...2000A	2000...30000A	3		T8V20PW
			4		T8V20PW-4
2500	1000...2500A	2500...37500A	3		T8V25PW
			4		T8V25PW
3000 ⁽¹⁾	1200...3000A	3000...45000A	3		T8V30PW
			4		T8V30PW-4

⁽¹⁾ Only available with rear vertical terminals for busbars

Standard PR332 LSI version

Electronic trip unit				IC	V
Frame size [A]	L adj. [A]	I adj. [A]	Poles	Rating (600V)	100 kA Part number
1600	640...1600A	1600...24000A	3		T8V16RW
			4		T8V16RW-4
2000	800...2000A	2000...30000A	3		T8V20RW
			4		T8V20RW-4
2500	1000...2500A	2500...37500A	3		T8V25RW
			4		T8V25RW
3000 ⁽¹⁾	1200...3000A	3000...45000A	3		T8V30RW
			4		T8V30RW-4

⁽¹⁾ Only available with rear vertical terminals for busbars