

Catalog Number: T6N800TW
UPC Number: 80432532967
Status: Active

Circuit Breaker TMAX T6N 800 UL/CSA fixed three-pole with front terminals and thermo-magnetic release tma r 800 i3=4000...8000 a

North American Specifications (UNSPSC)

| | |
|------------------|---|
| UNSPSC | 39121616 Molded case circuit breakers |
| IGCC | 4927 Molded case circuit breakers |
| Brand Name | ABB |
| Sub Brand | Tmax |
| Type | Molded case circuit breaker |
| Special Features | Features: The T6 Breaker Is An 800 AMP Frame With Either A Microprocessor Based Over Current Protective Trip System Or A Thermal Magnetic Trip Unit; The T6 Is Available As A 600 Or 800 A Frame; Interrupting Rating Class/breaking Capacity: Normal; Mechanical Life: 20000 Operations; Weight: 20.900 LB; T6n800tw: BKR T6N 800A 3P T/M UL LVP |
| Standard | UL 489, CSA, IEC 60947-2 |
| Current Rating | 800A |
| Frame | 600A, 800A |
| Trip Type | Thermal-magnetic |
| Interrupt Rating | Normal |
| Connection | None |

Packaging

| | |
|---------------------------|-----------------|
| Outer Quantity | 1 |
| Outer Dimensions (inches) | 14.7x1x11.7 |
| Weight Uom | 20.71 lbs. Each |

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com