

AC Toggle Switch

AH18221I-C

UPC:040893657387

Dimensions:

- **Height:** 3.28 IN
- **Length:** 1.36 IN
- **Width:** 1.05 IN

Weight: .21 LB

Warranties: No Data

Specifications:

- **Type:** Toggle switch
- **Allowable Wire Size:** #14-10 AWG
- **Amperage Rating:** 20A
- **Application:** Industrial
- **Mounting Type:** Flush
- **Voltage Rating:** 347V
- **Wiring Method:** Back and side
- **Connector Type:** Screw
- **Color:** Ivory
- **Load Type:** Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen
- **Number Of Poles:** Single-pole
- **Material:** Polycarbonate

Supporting documents:

- [Wiring Devices Buyers Guide](#)

Certifications:

- cUL Listed

Product compliance: No Data

