
CO1 Multi-gang

200 A (main lugs), 100 A per position 120/240 V; multi-gang combination with or without breaker

Product specifications

- Conductor range: line: 6 AWG-250 kcmil, load: 6-1/0 AWG
- Overhead only tunnel type connectors for both load and line sides
- Underground only aluminum tunnel type connector load side (6–1/0 AWG), line side ½ in. studs
- Supplied with screw type rings
- · Weatherproof Type 3R enclosure

- Bottom compartment has provision for 2 pole circuit breaker (max 100 A) 10 kA breakers (22 kA breaker where indicated HI) Siemens (Q), Eaton (BR), GE (TQL). Only SQD (QO) breakers will fit units with suffix SD.
- Primarily used in: All provinces



Diagrams

